

Humasis




# HUMASIS Urinalysis

U-AQ smart / U-AQ core / U-AQS

# Urine Chemistry Analyzer more Accurate & Quicker



Technical Specifications	
Operating mode	Semi-automatic urine analyzer
Dimension	275x250x170mm
Weight	1.3 kg
Power	100-250V, 3A
Oper. Conditions	Temp. : 2°C-30°C / Humi. : 10%-70%
Method	Reflectance photometer
Test Capacity	300Tests/hour(Max. 800tests)
Memory Capacity	2,000 Samples
Interface	RS232C, PS/2





## Core U=AQ 50Tests/h

Technical Specifications	
Operating mode	Semi-automatic urine analyzer
Dimension	300x250x90mm
Weight	1.2 kg
Power	100-250V, 2A
Oper. Conditions	Temp. : 2°C-30°C / Humi. : 10%-70%
Method	Reflectance photometer
Test Capacity	50Tests/hour(Max. 120tests)
Memory Capacity	2,000 Samples
Interface	RS232C, PS/2

# U-AQS

## Reagent Strips for Urinilysis

- Fast result visually or instrumentally
- High accuracy and reproducibility
- No interference in various conditions
- Quick Results(all reagent pads are read at one time, between one and two minutes after dipping).
- Good resistance to humidity
- Long shelf life : 24 months
- Unusual color of urine can be reported and compensated
- kFDA & CE marked



Products	Cat. No.	Urinalysis Strips										
U-AQ 1P	AUS1P-3100											
U-AQ 2GP	AUS2GP-3100		—									
U-AQ 3	AUS3-3100		—									
U-AQ 3GK	AUS3GK-3100		—	—								
U-AQ 4	AUS4-3100		—				—					
U-AQ 4SG	AUS4SG-3100		—		—			—				
U-AQ 5	AUS5-3100		—	—			—					
U-AQ 10	AUS10-3100		—	—	—	—	—	—	—	—	—	—
U-AQ 11	AUS11-3100	—	—	—	—	—	—	—	—	—	—	—
Quality Controls												
Level I	Liquicheck Controls	N/A	Neg.	Neg.	Neg.	1.010~1.020	Neg.	5.0~6.0	Neg.	Norm.	Neg.	Neg.
Level II	Liquicheck Controls	N/A	±/---4+ (100~2000 mg/dL)	1+~2+	±/---2+ (5~40 mg/dL)	1.010~1.015	±/---3+ (10~200 RBC/μL)	6.5~8.0	±/---3+ (15~300 RBC/μL)	2~8 mg/dL	Pos.	±/---3+ (15~500 μL/dL)

Abb.: Neg., negative; Pos., positive; Norm., normal

# Humasis

## Ordering Information

### U-AQ

Product	Cat. No.	Quantity/Set			
U-AQ smart	AAQ-8011	300/Set	* option : Keyboard / Barcode Reader		
AC Adapter 1EA (100-240V / 12VDC 3A)	Power cable 1EA	Thermal Printer paper 2 Roll	User Manual 1EA	Plate 2EA	RS 232C Cable 1EA

Product	Cat. No.	Quantity/Set			
U-AQ core	AAQ-8010	50/Set	* option : Keyboard / Barcode Reader		
AC Adapter 1EA (100-240V / 12VDC 3A)	Power cable 1EA	Thermal Printer paper 2 Roll	User Manual 1EA	User's program CD 1EA	RS 232C Cable 1EA

### U-AQS

Product	Cat. No.	Quantity/Bottle	Product	Cat. No.	Quantity/Bottle
U-AQS 1P	AUS1P-3100	100T	U-AQS 4SG	AUS4SG-3100	100T
U-AQS 2GP	AUS2GP-3100	100T	U-AQS 5	AUS5-3100	100T
U-AQS 3	AUS3-3100	100T	U-AQS 10	AUS10-3100	100T
U-AQS 3GK	AUS3GK-3100	100T	U-AQS 11	AUS11-3100	100T
U-AQS 4	AUS4-3100	100T			

## Contact information

- HUMASIS CO., LTD.
- Rm. 504 SHINWON VISION TOWER 88 Jeonpa-ro,  
Dongan-gu, Anyang-si Gyeonggi-do, 431-080, KOREA
- Tel: +82-31-478-8591
- Fax: +82-31-478-8586
- Purchase Product: +82-31-478-8591,  
e-mail: [question@humasis.com](mailto:question@humasis.com)
- Technical Service: +82-31-478-8595,  
e-mail: [customerservice@humasis.com](mailto:customerservice@humasis.com)

For more information, please visit our website  
[www.humasis.com](http://www.humasis.com)